

TC389

P30.12 66

MCU\_DO\_VT\_MN\_OD

MCU\_QUC MCU\_QT2

TC389

P25.8  
P25.9  
P25.10

P25.0  
P25.1  
P25.2  
P25.3  
P25.4  
P25.5  
P25.6  
P25.7

P25.11

MCU\_DO\_HS\_DIS  
MCU\_DO\_HS\_CS  
MCU\_DO\_HS\_WR  
MCU\_DO\_HS\_0  
MCU\_DO\_HS\_1  
MCU\_DO\_HS\_2  
MCU\_DO\_HS\_3  
MCU\_DO\_HS\_4  
MCU\_DO\_HS\_5  
MCU\_DO\_HS\_6  
MCU\_DO\_HS\_7  
MCU\_DO\_HS\_DIAG

HR428  
HR429

ISC1 1nF  
10% 3KV

Moat

MCU\_QUC

+5V\_ISO

EXT\_DO\_POWER

