

Product brief

64-Mbit to 512-Mbit HYPERRAM[™] 2.0/3.0 psuedostatic RAM memory

Overview

HYPERRAM[™] is a high-speed, low-pin-count, low-power self-refresh Dynamic RAM (DRAM) for high-performance embedded systems requiring expansion memory for scratchpad or buffering purposes.

HYPERRAM products support JEDEC JESD251 profile compliant HYPERBUS[™] and Octal xSPI interfaces that draw upon the legacy features of both parallel and serial interface memories, while enhancing system performance and ease of design, as well as reducing system cost. The low-pin count architecture make HYPERRAM especially suitable for power and board space constrained applications requiring off-chip external RAM.

Introduced in 2015, HYPERRAM now has a broad ecosystem support from leading MCU, MPU and FPGA chipset partners and customers. Optimized HYPERBUS[™] memory controller is available from multiple third-party IP vendors.

OCTAL xSPI RAM 64-Mbit to 512-Mbit | 400 MBps











HYPERBUS interface

- > HYPERBUS is a high-bandwidth, 12 pin interface that transfers information at double data rate (DDR), delivering bandwidth of up to 400 MBps.
- > The HYPERBUS interface enables a small 48-mm² 24-ball package which shares a common footprint with HYPERFLASH[™] products.
- > HYPERBUS is supported by a wide ecosystem of host controllers and memory types.

DRAM and FLASH on the same Bus

- > Reducing pin count simplies design complexity and decreases system cost.
- > HYPERFLASH and HYPERRAM 2.0 can be placed on the same bus and only require 13 pins for data transactions (12-pin HYPERBUS + 1 additional chip-select for the second memory device).

Key Benefits


High Reliability


- > Support for extended industrial and automotive Grade 1 & 2 temperature ranges.
- AEC-Q100-qualified parts and PPAP support available.

Target Applications

- > Automotive Instrument Clusters, Infotainment & Telematics Systems.
- > Industrial Machine Vision.
- > Industrial and Consumer HMI Display Panels.
- > Consumer Wearable Devices.
- IoT Gateways and Communication Modules.

64-Mbit to 512-Mbit HYPERRAM 2.0/3.0 psuedostatic RAM memory





64-Mbit HYPERRAM Memory Block Diagram

Operating on a Single HYPERBUS Simplifies Designs and Reduces Pin Count

Family	Data-bus width	Interface	Speed	Voltage	Density	MPN	Bandwidth	Temperature range	Package
HYPERRAM 2.0	8-bit	HyperBus (x8)	200 MHz	1.8V	64-Mbit	S27KS0642	400 MBps	I, V, A, B, M	24-ball BGA (6 mm x 8 mm)
					128-Mbit	S70KS1282	400 MBps	I, V, A, B, M	
					256-Mbit	\$80K\$2562	400 MBps	I, V, A, B, M	
					512-Mbit	S80KS5122	400 MBps	I, V, A, B, M	
			200 MHz, 166 MHz	3.0V	64-Mbit	S27KL0642	400 MBps, 333 MBps	I, V, A, B, M	
					128-Mbit	S70KL1282	400 MBps, 333 MBps	I, V, A, B, M	
Octal xSPI RAM		Octal xSPI (x8)	200 MHz	1.8V	64-Mbit	S27KS0643	400 MBps	I, V, A, B	
					128-Mbit	S70KS1283	400 MBps	I, V, A, B	
					256-Mbit	S80KS2563	400 MBps	I, V, A, B, M	
					512-Mbit	S80KS5123	400 MBps	I, V, A, B, M	
			200 MHz, 166 MHz	3.0V	64-Mbit	S27KL0643	400 MBps, 333 MBps	I, V, A, B	
					128-Mbit	S70KL1283	400 MBps, 333 MBps	I, V, A, B	
HYPERRAM 3.0	16-bit	HyperBus Extended I/O (x16)	200 MHz	1.8V	256-Mbit	S80KS2564	800 MBps	Ι, V	49-ball BGA (8 mm x 8 mm)

HYPERRAM 2.0 memory device portfolio

To learn more about HYPERRAM[™] Memory products, visit www.infineon.com/HYPERRAM

Published by Infineon Technologies AG 81726 Munich, Germany

© 2021 Infineon Technologies AG. All Rights Reserved.

Please note!

This Document is for information purposes only and any information given herein shall in no event be regarded as a warranty, guarantee or description of any functionality, conditions and/or quality of our products or any suitability for a particular purpose. With regard to the technical specifications of our products, we kindly ask you to refer to the relevant product data sheets provided by us. Our customers and their technical departments are required to evaluate the suitability of our products for the intended application.

We reserve the right to change this document and/or the information given herein at any time.

Additional information

For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices, please contact your nearest Infineon Technologies office (www.infineon.com).

Warnings

Due to technical requirements, our products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by us in a written document signed by authorized representatives of Infineon Technologies, our products may not be used in any lifeendangering applications, including but not limited to medical, nuclear, military, life-critical or any other applications where a failure of the product or any consequences of the use thereof can result in personal injury.