



THIS SPEC IS OBSOLETE

Spec No: 002-05092

Spec Title: Errata of S6E1A1 Series, Datasheet

Replaced by: NONE

S6E1A1 Series

32-BIT Microcontroller
FM0+ Family
Data Sheet

Errata Sheet



Errata of S6E1A1 Series, Datasheet

Page	Item	Description
Original document code: DS710-00001-1v0-E		
Rev. 1.0 September 25, 2017		
11,12	5. Pin Assignment	<p>The 30pin and 31pin of FPT-32P-M30 and LCC-32P-M73 should be corrected as indicated by the shaded below.</p> <p>(Error) 30pin: P61/SOT3_0/TIOB2_2/DTTI0X_2/SCS11_2 31pin: P60/SIN3_0/TIOA2_2/INT15_1/IC00_0/IGTRG0_0/SCS10_2</p> <p>(Correct) 30pin: P61/SOT3_0/TIOB2_2/DTTI0X_2 31pin: P60/SIN3_0/TIOA2_2/INT15_1/IC00_0/IGTRG0_0</p>

Page	Item	Description																																																																													
20	6. List of Pin Functions List of pin numbers	<p>The 30pin and 31pin of LQFP-32 and QFN-32 should be corrected as indicated by the shaded below.</p> <p>(Error)</p> <table border="1" style="width: 100%; border-collapse: collapse; margin-bottom: 10px;"> <thead> <tr> <th colspan="3" style="text-align: center;">Pin no.</th> <th rowspan="2" style="text-align: center;">Pin name</th> <th rowspan="2" style="text-align: center;">I/O circuit type</th> <th rowspan="2" style="text-align: center;">Pin state type</th> </tr> <tr> <th style="text-align: center;">LQFP-52</th> <th style="text-align: center;">LQFP-48 QFN-48</th> <th style="text-align: center;">LQFP-32 QFN-32</th> </tr> </thead> <tbody> <tr> <td rowspan="4" style="text-align: center;">47</td> <td rowspan="4" style="text-align: center;">43</td> <td rowspan="4" style="text-align: center;">30</td> <td>P61</td> <td rowspan="4" style="text-align: center;">I*</td> <td rowspan="4" style="text-align: center;">I</td> </tr> <tr> <td>SOT3_0</td> </tr> <tr> <td>TIOB2_2</td> </tr> <tr> <td>DTTI0X_2</td> </tr> <tr> <td rowspan="6" style="text-align: center;">48</td> <td rowspan="6" style="text-align: center;">44</td> <td rowspan="6" style="text-align: center;">31</td> <td>SCS11_2</td> <td rowspan="6" style="text-align: center;">I*</td> <td rowspan="6" style="text-align: center;">J</td> </tr> <tr> <td>P60</td> </tr> <tr> <td>SIN3_0</td> </tr> <tr> <td>TIOA2_2</td> </tr> <tr> <td>INT15_1</td> </tr> <tr> <td>IC00_0</td> </tr> <tr> <td>IGTRG0_0</td> </tr> <tr> <td></td> <td></td> <td></td> <td>SCS10_2</td> <td></td> <td></td> </tr> </tbody> </table> <p>(Correct)</p> <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th colspan="3" style="text-align: center;">Pin no.</th> <th rowspan="2" style="text-align: center;">Pin name</th> <th rowspan="2" style="text-align: center;">I/O circuit type</th> <th rowspan="2" style="text-align: center;">Pin state type</th> </tr> <tr> <th style="text-align: center;">LQFP-52</th> <th style="text-align: center;">LQFP-48 QFN-48</th> <th style="text-align: center;">LQFP-32 QFN-32</th> </tr> </thead> <tbody> <tr> <td rowspan="4" style="text-align: center;">47</td> <td rowspan="4" style="text-align: center;">43</td> <td rowspan="4" style="text-align: center;">30</td> <td>P61</td> <td rowspan="4" style="text-align: center;">I*</td> <td rowspan="4" style="text-align: center;">I</td> </tr> <tr> <td>SOT3_0</td> </tr> <tr> <td>TIOB2_2</td> </tr> <tr> <td>DTTI0X_2</td> </tr> <tr> <td rowspan="6" style="text-align: center;">48</td> <td rowspan="6" style="text-align: center;">44</td> <td rowspan="6" style="text-align: center;">31</td> <td>SCS11_2</td> <td rowspan="6" style="text-align: center;">I*</td> <td rowspan="6" style="text-align: center;">J</td> </tr> <tr> <td>P60</td> </tr> <tr> <td>SIN3_0</td> </tr> <tr> <td>TIOA2_2</td> </tr> <tr> <td>INT15_1</td> </tr> <tr> <td>IC00_0</td> </tr> <tr> <td></td> <td></td> <td></td> <td>IGTRG0_0</td> <td></td> <td></td> </tr> <tr> <td></td> <td></td> <td></td> <td>SCS10_2</td> <td></td> <td></td> </tr> </tbody> </table>	Pin no.			Pin name	I/O circuit type	Pin state type	LQFP-52	LQFP-48 QFN-48	LQFP-32 QFN-32	47	43	30	P61	I*	I	SOT3_0	TIOB2_2	DTTI0X_2	48	44	31	SCS11_2	I*	J	P60	SIN3_0	TIOA2_2	INT15_1	IC00_0	IGTRG0_0				SCS10_2			Pin no.			Pin name	I/O circuit type	Pin state type	LQFP-52	LQFP-48 QFN-48	LQFP-32 QFN-32	47	43	30	P61	I*	I	SOT3_0	TIOB2_2	DTTI0X_2	48	44	31	SCS11_2	I*	J	P60	SIN3_0	TIOA2_2	INT15_1	IC00_0				IGTRG0_0						SCS10_2		
Pin no.			Pin name	I/O circuit type	Pin state type																																																																										
LQFP-52	LQFP-48 QFN-48	LQFP-32 QFN-32																																																																													
47	43	30	P61	I*	I																																																																										
			SOT3_0																																																																												
			TIOB2_2																																																																												
			DTTI0X_2																																																																												
48	44	31	SCS11_2	I*	J																																																																										
			P60																																																																												
			SIN3_0																																																																												
			TIOA2_2																																																																												
			INT15_1																																																																												
			IC00_0																																																																												
IGTRG0_0																																																																															
			SCS10_2																																																																												
Pin no.			Pin name	I/O circuit type	Pin state type																																																																										
LQFP-52	LQFP-48 QFN-48	LQFP-32 QFN-32																																																																													
47	43	30	P61	I*	I																																																																										
			SOT3_0																																																																												
			TIOB2_2																																																																												
			DTTI0X_2																																																																												
48	44	31	SCS11_2	I*	J																																																																										
			P60																																																																												
			SIN3_0																																																																												
			TIOA2_2																																																																												
			INT15_1																																																																												
			IC00_0																																																																												
			IGTRG0_0																																																																												
			SCS10_2																																																																												

Page	Item	Description																																																														
23	6. List of Pin Functions List of pin functions	<p>The SCS10_2 and SCS11_2 of LQFP-32 and QFN-32 should be corrected as indicated by the shaded below.</p> <p>(Error)</p> <table border="1"> <thead> <tr> <th rowspan="2">Pin function</th> <th rowspan="2">Pin name</th> <th rowspan="2">Function description</th> <th colspan="3">Pin no.</th> </tr> <tr> <th>LQFP-52</th> <th>LQFP-48 QFN-48</th> <th>LQFP-32 QFN-32</th> </tr> </thead> <tbody> <tr> <td rowspan="2">Multi-function</td> <td>SCS10_1</td> <td>Multi-function serial interface ch.1</td> <td>31</td> <td>29</td> <td>-</td> </tr> <tr> <td>SCS10_2</td> <td>serial chip select 0 output/input pin.</td> <td>48</td> <td>44</td> <td>31</td> </tr> <tr> <td rowspan="2">Serial 1</td> <td>SCS11_1</td> <td>Multi-function serial interface ch.1</td> <td>32</td> <td>30</td> <td>-</td> </tr> <tr> <td>SCS11_2</td> <td>serial chip select 1 output pin.</td> <td>47</td> <td>43</td> <td>30</td> </tr> </tbody> </table> <p>(Correct)</p> <table border="1"> <thead> <tr> <th rowspan="2">Pin function</th> <th rowspan="2">Pin name</th> <th rowspan="2">Function description</th> <th colspan="3">Pin no.</th> </tr> <tr> <th>LQFP-52</th> <th>LQFP-48 QFN-48</th> <th>LQFP-32 QFN-32</th> </tr> </thead> <tbody> <tr> <td rowspan="2">Multi-function</td> <td>SCS10_1</td> <td>Multi-function serial interface ch.1</td> <td>31</td> <td>29</td> <td>-</td> </tr> <tr> <td>SCS10_2</td> <td>serial chip select 0 output/input pin.</td> <td>48</td> <td>44</td> <td style="background-color: #cccccc;">█</td> </tr> <tr> <td rowspan="2">Serial 1</td> <td>SCS11_1</td> <td>Multi-function serial interface ch.1</td> <td>32</td> <td>30</td> <td>-</td> </tr> <tr> <td>SCS11_2</td> <td>serial chip select 1 output pin.</td> <td>47</td> <td>43</td> <td style="background-color: #cccccc;">█</td> </tr> </tbody> </table>	Pin function	Pin name	Function description	Pin no.			LQFP-52	LQFP-48 QFN-48	LQFP-32 QFN-32	Multi-function	SCS10_1	Multi-function serial interface ch.1	31	29	-	SCS10_2	serial chip select 0 output/input pin.	48	44	31	Serial 1	SCS11_1	Multi-function serial interface ch.1	32	30	-	SCS11_2	serial chip select 1 output pin.	47	43	30	Pin function	Pin name	Function description	Pin no.			LQFP-52	LQFP-48 QFN-48	LQFP-32 QFN-32	Multi-function	SCS10_1	Multi-function serial interface ch.1	31	29	-	SCS10_2	serial chip select 0 output/input pin.	48	44	█	Serial 1	SCS11_1	Multi-function serial interface ch.1	32	30	-	SCS11_2	serial chip select 1 output pin.	47	43	█
Pin function	Pin name	Function description				Pin no.																																																										
			LQFP-52	LQFP-48 QFN-48	LQFP-32 QFN-32																																																											
Multi-function	SCS10_1	Multi-function serial interface ch.1	31	29	-																																																											
	SCS10_2	serial chip select 0 output/input pin.	48	44	31																																																											
Serial 1	SCS11_1	Multi-function serial interface ch.1	32	30	-																																																											
	SCS11_2	serial chip select 1 output pin.	47	43	30																																																											
Pin function	Pin name	Function description	Pin no.																																																													
			LQFP-52	LQFP-48 QFN-48	LQFP-32 QFN-32																																																											
Multi-function	SCS10_1	Multi-function serial interface ch.1	31	29	-																																																											
	SCS10_2	serial chip select 0 output/input pin.	48	44	█																																																											
Serial 1	SCS11_1	Multi-function serial interface ch.1	32	30	-																																																											
	SCS11_2	serial chip select 1 output pin.	47	43	█																																																											
58,60, 62,64	14. Electrical Characteristics 14.4 AC Characteristics 14.4.9 CSIO Timing	<p>The note of “Synchronous serial” should be corrected as indicated by the shaded below.</p> <p>(Error)</p> <ul style="list-style-type: none"> - <i>The characteristics are only applicable when the relocate port numbers are the same. For instance, they are not applicable for the combination of SCLKx_0 and SOTx_1.</i> <p>(Correct)</p> <ul style="list-style-type: none"> - <i>The characteristics are only applicable when the relocate port numbers are the same. For instance, they are not applicable for the combination of SCKx_0 and SOTx_1.</i> 																																																														
66,68, 70,72	14. Electrical Characteristics 14.4 AC Characteristics 14.4.9 CSIO Timing	<p>The note of “When using synchronous serial chip select” should be added as indicated by the shaded below.</p> <ul style="list-style-type: none"> - <i>The characteristics are only applicable when the relocate port numbers are the same. For instance, they are not applicable for the combination of SCKx_0 and SCSx0_1.</i> 																																																														

Page	Item	Description																																																																														
90	15. Ordering Information	<p>The ordering information should be corrected as indicated by the shaded below.</p> <p>(Error)</p> <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th>Part number</th> <th>Package</th> </tr> </thead> <tbody> <tr> <td>S6E1A11B0AGP2</td> <td rowspan="2">Plastic • LQFP (0.80 mm pitch), 32 pins (FPT-32P-M30)</td> </tr> <tr> <td>S6E1A12B0AGP2</td> </tr> <tr> <td>S6E1A11B0AGN2</td> <td rowspan="2">Plastic • QFN (0.50 mm pitch), 32 pins (LCC-32P-M73)</td> </tr> <tr> <td>S6E1A12B0AGN2</td> </tr> <tr> <td>S6E1A11C0AGV2</td> <td rowspan="2">Plastic • LQFP (0.50 mm pitch), 48 pins (FPT-48P-M49)</td> </tr> <tr> <td>S6E1A12C0AGV2</td> </tr> <tr> <td>S6E1A11C0AGN2</td> <td rowspan="2">Plastic • QFN (0.50 mm pitch), 48 pins (LCC-48P-M74)</td> </tr> <tr> <td>S6E1A12C0AGN2</td> </tr> <tr> <td>S6E1A11C0AGF2</td> <td rowspan="2">Plastic • LQFP (0.65 mm pitch), 52 pins (FPT-52P-M02)</td> </tr> <tr> <td>S6E1A12C0AGF2</td> </tr> </tbody> </table> <p>(Correct)</p> <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th>Part number</th> <th>On-chip Flash memory</th> <th>On-chip SRAM</th> <th>Package</th> <th>Packing</th> </tr> </thead> <tbody> <tr> <td>S6E1A11B0AGP20000</td> <td>56 Kbyte</td> <td>6 Kbyte</td> <td rowspan="2">Plastic • LQFP (0.80 mm pitch), 32 pins (FPT-32P-M30)</td> <td>Tray</td> </tr> <tr> <td>S6E1A12B0AGP20000</td> <td>88 Kbyte</td> <td>6 Kbyte</td> </tr> <tr> <td>S6E1A11B0AGN20000</td> <td>56 Kbyte</td> <td>6 Kbyte</td> <td rowspan="3">Plastic • QFN (0.50 mm pitch), 32 pins (LCC-32P-M73)</td> <td>Tray</td> </tr> <tr> <td>S6E1A12B0AGN20000</td> <td>88 Kbyte</td> <td>6 Kbyte</td> <td>Taping</td> </tr> <tr> <td>S6E1A11B0AGN2B000</td> <td>56 Kbyte</td> <td>6 Kbyte</td> </tr> <tr> <td>S6E1A12B0AGN2B000</td> <td>88 Kbyte</td> <td>6 Kbyte</td> <td rowspan="2">Plastic • LQFP (0.50 mm pitch), 48 pins (FPT-48P-M49)</td> <td>Tray</td> </tr> <tr> <td>S6E1A11C0AGV20000</td> <td>56 Kbyte</td> <td>6 Kbyte</td> </tr> <tr> <td>S6E1A12C0AGV20000</td> <td>88 Kbyte</td> <td>6 Kbyte</td> <td rowspan="4">Plastic • QFN (0.50 mm pitch), 48 pins (LCC-48P-M74)</td> <td>Tray</td> </tr> <tr> <td>S6E1A11C0AGN20000</td> <td>56 Kbyte</td> <td>6 Kbyte</td> <td>Taping</td> </tr> <tr> <td>S6E1A12C0AGN20000</td> <td>88 Kbyte</td> <td>6 Kbyte</td> </tr> <tr> <td>S6E1A11C0AGN2B000</td> <td>56 Kbyte</td> <td>6 Kbyte</td> </tr> <tr> <td>S6E1A12C0AGN2B000</td> <td>88 Kbyte</td> <td>6 Kbyte</td> <td rowspan="2">Plastic • LQFP (0.65 mm pitch), 52 pins (FPT-52P-M02)</td> <td>Tray</td> </tr> <tr> <td>S6E1A11C0AGF20000</td> <td>56 Kbyte</td> <td>6 Kbyte</td> </tr> <tr> <td>S6E1A12C0AGF20000</td> <td>88 Kbyte</td> <td>6 Kbyte</td> <td></td> <td></td> </tr> </tbody> </table>	Part number	Package	S6E1A11B0AGP2	Plastic • LQFP (0.80 mm pitch), 32 pins (FPT-32P-M30)	S6E1A12B0AGP2	S6E1A11B0AGN2	Plastic • QFN (0.50 mm pitch), 32 pins (LCC-32P-M73)	S6E1A12B0AGN2	S6E1A11C0AGV2	Plastic • LQFP (0.50 mm pitch), 48 pins (FPT-48P-M49)	S6E1A12C0AGV2	S6E1A11C0AGN2	Plastic • QFN (0.50 mm pitch), 48 pins (LCC-48P-M74)	S6E1A12C0AGN2	S6E1A11C0AGF2	Plastic • LQFP (0.65 mm pitch), 52 pins (FPT-52P-M02)	S6E1A12C0AGF2	Part number	On-chip Flash memory	On-chip SRAM	Package	Packing	S6E1A11B0AGP20000	56 Kbyte	6 Kbyte	Plastic • LQFP (0.80 mm pitch), 32 pins (FPT-32P-M30)	Tray	S6E1A12B0AGP20000	88 Kbyte	6 Kbyte	S6E1A11B0AGN20000	56 Kbyte	6 Kbyte	Plastic • QFN (0.50 mm pitch), 32 pins (LCC-32P-M73)	Tray	S6E1A12B0AGN20000	88 Kbyte	6 Kbyte	Taping	S6E1A11B0AGN2B000	56 Kbyte	6 Kbyte	S6E1A12B0AGN2B000	88 Kbyte	6 Kbyte	Plastic • LQFP (0.50 mm pitch), 48 pins (FPT-48P-M49)	Tray	S6E1A11C0AGV20000	56 Kbyte	6 Kbyte	S6E1A12C0AGV20000	88 Kbyte	6 Kbyte	Plastic • QFN (0.50 mm pitch), 48 pins (LCC-48P-M74)	Tray	S6E1A11C0AGN20000	56 Kbyte	6 Kbyte	Taping	S6E1A12C0AGN20000	88 Kbyte	6 Kbyte	S6E1A11C0AGN2B000	56 Kbyte	6 Kbyte	S6E1A12C0AGN2B000	88 Kbyte	6 Kbyte	Plastic • LQFP (0.65 mm pitch), 52 pins (FPT-52P-M02)	Tray	S6E1A11C0AGF20000	56 Kbyte	6 Kbyte	S6E1A12C0AGF20000	88 Kbyte	6 Kbyte		
Part number	Package																																																																															
S6E1A11B0AGP2	Plastic • LQFP (0.80 mm pitch), 32 pins (FPT-32P-M30)																																																																															
S6E1A12B0AGP2																																																																																
S6E1A11B0AGN2	Plastic • QFN (0.50 mm pitch), 32 pins (LCC-32P-M73)																																																																															
S6E1A12B0AGN2																																																																																
S6E1A11C0AGV2	Plastic • LQFP (0.50 mm pitch), 48 pins (FPT-48P-M49)																																																																															
S6E1A12C0AGV2																																																																																
S6E1A11C0AGN2	Plastic • QFN (0.50 mm pitch), 48 pins (LCC-48P-M74)																																																																															
S6E1A12C0AGN2																																																																																
S6E1A11C0AGF2	Plastic • LQFP (0.65 mm pitch), 52 pins (FPT-52P-M02)																																																																															
S6E1A12C0AGF2																																																																																
Part number	On-chip Flash memory	On-chip SRAM	Package	Packing																																																																												
S6E1A11B0AGP20000	56 Kbyte	6 Kbyte	Plastic • LQFP (0.80 mm pitch), 32 pins (FPT-32P-M30)	Tray																																																																												
S6E1A12B0AGP20000	88 Kbyte	6 Kbyte																																																																														
S6E1A11B0AGN20000	56 Kbyte	6 Kbyte	Plastic • QFN (0.50 mm pitch), 32 pins (LCC-32P-M73)	Tray																																																																												
S6E1A12B0AGN20000	88 Kbyte	6 Kbyte		Taping																																																																												
S6E1A11B0AGN2B000	56 Kbyte	6 Kbyte																																																																														
S6E1A12B0AGN2B000	88 Kbyte	6 Kbyte	Plastic • LQFP (0.50 mm pitch), 48 pins (FPT-48P-M49)	Tray																																																																												
S6E1A11C0AGV20000	56 Kbyte	6 Kbyte																																																																														
S6E1A12C0AGV20000	88 Kbyte	6 Kbyte	Plastic • QFN (0.50 mm pitch), 48 pins (LCC-48P-M74)	Tray																																																																												
S6E1A11C0AGN20000	56 Kbyte	6 Kbyte		Taping																																																																												
S6E1A12C0AGN20000	88 Kbyte	6 Kbyte																																																																														
S6E1A11C0AGN2B000	56 Kbyte	6 Kbyte																																																																														
S6E1A12C0AGN2B000	88 Kbyte	6 Kbyte	Plastic • LQFP (0.65 mm pitch), 52 pins (FPT-52P-M02)	Tray																																																																												
S6E1A11C0AGF20000	56 Kbyte	6 Kbyte																																																																														
S6E1A12C0AGF20000	88 Kbyte	6 Kbyte																																																																														

Document History Page

Document Title: Errata of S6E1A1 Series, Datasheet			
Document Number: 002-05092			
Rev.	ECN No.	Orig. of Change	Description of Change
**	-	AKIH	Initial release
*A	5895081	HUAL	Obsolete document. Completing Sunset Review.