

## SIPMOS® Small-Signal-Transistor


## BSP 320S

### Features

- N channel
- Enhancement mode
- Avalanche rated
- $dv/dt$  rated

### Product Summary

|                                  |              |      |          |
|----------------------------------|--------------|------|----------|
| Drain source voltage             | $V_{DS}$     | 60   | V        |
| Drain-Source on-state resistance | $R_{DS(on)}$ | 0.12 | $\Omega$ |
| Continuous drain current         | $I_D$        | 2.9  | A        |



| Type    | Package | Ordering Code |
|---------|---------|---------------|
| BSP320S | SOT-223 | Q67000-S4001  |

| Pin 1 | Pin 2/4 | Pin 3 |
|-------|---------|-------|
| G     | D       | S     |

**Maximum Ratings** , at  $T_j = 25\text{ °C}$ , unless otherwise specified

| Parameter   | Symbol       | Value        | Unit              |
|---|--------------|--------------|-------------------|
| Continuous drain current  | $I_D$        | 2.9          | A                 |
| Pulsed drain current<br>$T_A = 25\text{ °C}$  | $I_{Dpulse}$ | 11.6         |                   |
| Avalanche energy, single pulse<br>$I_D = 2.9\text{ A}$ , $V_{DD} = 25\text{ V}$ , $R_{GS} = 25\ \Omega$                                     | $E_{AS}$     | 60           | mJ                |
| Avalanche current, periodic limited by $T_{jmax}$   | $I_{AR}$     | 2.9          | A                 |
| Avalanche energy, periodic limited by $T_{jmax}$  | $E_{AR}$     | 0.18         | mJ                |
| Reverse diode $dv/dt$<br>$I_S = 2.9\text{ A}$ , $V_{DS} = 20\text{ V}$ , $di/dt = 200\text{ A}/\mu\text{s}$ ,<br>$T_{jmax} = 150\text{ °C}$ | $dv/dt$      | 6            | kV/ $\mu\text{s}$ |
| Gate source voltage   | $V_{GS}$     | $\pm 20$     | V                 |
| Power dissipation<br>$T_A = 25\text{ °C}$   | $P_{tot}$    | 1.8          | W                 |
| Operating temperature   | $T_j$        | -55 ... +150 | °C                |
| Storage temperature   | $T_{stg}$    | -55 ... +150 |                   |
| IEC climatic category; DIN IEC 68-1   |              | 55/150/56    |                   |

**Electrical Characteristics**

| Parameter  | Symbol | Values |      |      | Unit |
|--|--------|--------|------|------|------|
|  |        | min.   | typ. | max. |      |
| at $T_j = 25\text{ }^\circ\text{C}$ , unless otherwise specified |        |        |      |      |      |

**Thermal Characteristics**

|  |            |   |     |    |     |
|--|------------|---|-----|----|-----|
| Thermal resistance, junction - soldering point (Pin 4) | $R_{thJS}$ | - | 17  | -  | K/W |
| SMD version, device on PCB:                            | $R_{thJA}$ |   |     |    | K/W |
| @ min. footprint                                       |            | - | 110 | -  |     |
| @ 6 cm <sup>2</sup> cooling area <sup>1)</sup>         |            | - | -   | 70 |     |

**Static Characteristics**

|  |               |     |      |      |               |
|--|---------------|-----|------|------|---------------|
| Drain- source breakdown voltage<br>$V_{GS} = 0\text{ V}$ , $I_D = 0.25\text{ mA}$  | $V_{(BR)DSS}$ | 60  | -    | -    | V             |
| Gate threshold voltage, $V_{GS} = V_{DS}$<br>$I_D = 20\text{ }\mu\text{A}$   | $V_{GS(th)}$  | 2.1 | 3    | 4    |               |
| Zero gate voltage drain current<br>$V_{DS} = 60\text{ V}$ , $V_{GS} = 0\text{ V}$ , $T_j = 25\text{ }^\circ\text{C}$<br>$V_{DS} = 60\text{ V}$ , $V_{GS} = 0\text{ V}$ , $T_j = 150\text{ }^\circ\text{C}$ | $I_{DSS}$     | -   | 0.1  | 1    | $\mu\text{A}$ |
| Gate-source leakage current<br>$V_{GS} = 20\text{ V}$ , $V_{DS} = 0\text{ V}$  | $I_{GSS}$     | -   | 10   | 100  | nA            |
| Drain-Source on-state resistance<br>$V_{GS} = 10\text{ V}$ , $I_D = 2.9\text{ A}$  | $R_{DS(on)}$  | -   | 0.09 | 0.12 | $\Omega$      |

<sup>1</sup> Device on 50mm\*50mm\*1.5mm epoxy PCB FR4 with 6 cm<sup>2</sup> (one layer, 70 $\mu\text{m}$  thick) copper area for drain connection. PCB is vertical without blown air.

**Electrical Characteristics**

| Parameter<br>at $T_j = 25\text{ }^\circ\text{C}$ , unless otherwise specified   | Symbol       | Values |      |      | Unit |
|---|--------------|--------|------|------|------|
|   |              | min.   | typ. | max. |      |
| <b>Dynamic Characteristics</b>  |              |        |      |      |      |
| Transconductance<br>$V_{DS} \geq 2 \cdot I_D \cdot R_{DS(on)max}$ , $I_D = 2.9\text{ A}$                                    | $g_{fs}$     | 2.5    | 5.8  | -    | S    |
| Input capacitance<br>$V_{GS} = 0\text{ V}$ , $V_{DS} = 25\text{ V}$ , $f = 1\text{ MHz}$                                    | $C_{iss}$    | -      | 275  | 340  | pF   |
| Output capacitance<br>$V_{GS} = 0\text{ V}$ , $V_{DS} = 25\text{ V}$ , $f = 1\text{ MHz}$                                   | $C_{oss}$    | -      | 90   | 120  |      |
| Reverse transfer capacitance<br>$V_{GS} = 0\text{ V}$ , $V_{DS} = 25\text{ V}$ , $f = 1\text{ MHz}$                         | $C_{rss}$    | -      | 50   | 65   |      |
| Turn-on delay time<br>$V_{DD} = 30\text{ V}$ , $V_{GS} = 10\text{ V}$ , $I_D = 2.9\text{ A}$ ,<br>$R_G = 33\text{ }\Omega$  | $t_{d(on)}$  | -      | 11   | 17   | ns   |
| Rise time<br>$V_{DD} = 30\text{ V}$ , $V_{GS} = 10\text{ V}$ , $I_D = 2.9\text{ A}$ ,<br>$R_G = 33\text{ }\Omega$           | $t_r$        | -      | 25   | 40   |      |
| Turn-off delay time<br>$V_{DD} = 30\text{ V}$ , $V_{GS} = 10\text{ V}$ , $I_D = 2.9\text{ A}$ ,<br>$R_G = 33\text{ }\Omega$ | $t_{d(off)}$ | -      | 25   | 40   |      |
| Fall time<br>$V_{DD} = 30\text{ V}$ , $V_{GS} = 10\text{ V}$ , $I_D = 2.9\text{ A}$ ,<br>$R_G = 33\text{ }\Omega$           | $t_f$        | -      | 35   | 55   |      |

**Electrical Characteristics**


| Parameter<br>at $T_j = 25\text{ }^\circ\text{C}$ , unless otherwise specified   | Symbol          | Values |      |      | Unit |
|---|-----------------|--------|------|------|------|
|   |                 | min.   | typ. | max. |      |
| <b>Dynamic Characteristics</b>  |                 |        |      |      |      |
| Gate charge at threshold<br>$V_{DD} = 40\text{ V}$ , $I_D = 0.1\text{ A}$ , $V_{GS} = 1\text{ V}$                       | $Q_{G(th)}$     | -      | 0.25 | 0.3  | nC   |
| Gate charge at $V_{GS}=7\text{ V}$<br>$V_{DD} = 40\text{ V}$ , $I_D = 2.9\text{ A}$ , $V_{GS} = 0\text{ to }7\text{ V}$ | $Q_{g(7)}$      | -      | 7.4  | 9.3  | nC   |
| Gate charge total<br>$V_{DD} = 40\text{ V}$ , $I_D = 2.9\text{ A}$ , $V_{GS} = 0\text{ to }10\text{ V}$                 | $Q_g$           | -      | 9.7  | 12   |      |
| Gate plateau voltage<br>$V_{DD} = 40\text{ V}$ , $I_D = 2.9\text{ A}$   | $V_{(plateau)}$ | -      | 4.7  | -    | V    |

**Reverse Diode**

|   |          |   |      |      |               |
|---|----------|---|------|------|---------------|
| Inverse diode continuous forward current<br>$T_A = 25\text{ }^\circ\text{C}$                      | $I_S$    | - | -    | 2.9  | A             |
| Inverse diode direct current,pulsed<br>$T_A = 25\text{ }^\circ\text{C}$                           | $I_{SM}$ | - | -    | 11.6 |               |
| Inverse diode forward voltage<br>$V_{GS} = 0\text{ V}$ , $I_F = 5.8\text{ A}$                     | $V_{SD}$ | - | 0.95 | 1.2  | V             |
| Reverse recovery time<br>$V_R = 30\text{ V}$ , $I_F=I_S$ , $di_F/dt = 100\text{ A}/\mu\text{s}$   | $t_{rr}$ | - | 45   | 56   | ns            |
| Reverse recovery charge<br>$V_R = 30\text{ V}$ , $I_F=I_S$ , $di_F/dt = 100\text{ A}/\mu\text{s}$ | $Q_{rr}$ | - | 0.08 | 0.12 | $\mu\text{C}$ |


**Power Dissipation**

$$P_{tot} = f(T_A)$$



**Drain current**


$$I_D = f(T_A)$$



**Safe operating area**

$$I_D = f(V_{DS})$$


parameter :  $D = 0$  ,  $T_A = 25\text{ }^\circ\text{C}$



**Transient thermal impedance**

$$Z_{thJA} = f(t_p)$$


parameter :  $D = t_p/T$



**Typ. output characteristics**

$$I_D = f(V_{DS})$$


parameter:  $t_p = 80 \mu s$



**Drain-source on-resistance**

$$R_{DS(on)} = f(T_j)$$


parameter:  $I_D = 2.9 A, V_{GS} = 10 V$



**Typ. transfer characteristics  $I_D = f(V_{GS})$**

parameter:  $t_p = 80 \mu s$


$V_{DS} \geq 2 \times I_D \times R_{DS(on)max}$



**Gate threshold voltage**

$V_{GS(th)} = f(T_j)$


parameter:  $V_{GS} = V_{DS}, I_D = 20 \mu A$



**Typ. capacitances**

$C = f(V_{DS})$


Parameter:  $V_{GS} = 0 V, f = 1 MHz$



**Forward characteristics of reverse diode**

$I_F = f(V_{SD})$


parameter:  $T_j, t_p = 80 \mu s$



**Avalanche Energy  $E_{AS} = f(T_j)$**

parameter:  $I_D = 2.9\text{ A}$ ,  $V_{DD} = 25\text{ V}$


$R_{GS} = 25\ \Omega$



**Typ. gate charge**

$V_{GS} = f(Q_{Gate})$

parameter:  $I_{D\text{ puls}} = 2.9\text{ A}$



**Drain-source breakdown voltage**

$V_{(BR)DSS} = f(T_j)$

